



On Line Catalog



<b>BURNDY Catalog Number</b>	C11D
<b>UPC Number</b>	781810142349
<b>Description</b>	1/2-1 BARE DIR. BURIAL
<b>Status</b>	Active

**Web Use**  
BURNDY Product Line

Pipe Size (Range)	1/2 in-1 in
Width (in)	0.63
Length (in)	2.25
Height (in)	1.81
Pad Width (in)	0.63

**Dimensional**

**General**

Product Description	Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1/2" - 1" Water Pipe, #4 - #8 Rebar
---------------------	---

**Conductor(s)**

Copper Solid Size (Range)	10 AWG-2 AWG
Copper Stranded (Range)	10 AWG-2 AWG
Rebar Size (Range)	4 -8

**Physical**

Type of Hardware	DURIUM& Silicon Bronze
Type of Plating	Unplated
Ground Strap	N
Plated (Yes or No)	N
For Armored Cable	N
Product Material	Bronze Alloy
Recommended Installation Torque - Wire Clamp	50
Recommended Installation Torque - Pipe	50

**Approvals / Certifications**

UL Listed	Y
CSA Certified	Y
Rated for Direct Burial	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47, industrial Park Drive  
Manchester NH03109

**BURNDY Technical Servcies**

47, industrial Park Drive  
Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
Monday - Friday  
Phone: 000-346-4175