



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

C11N
 781810142288
 GRD CL BARE WIRE 1/2-1IN
 Active

Web Use
 BURNDY Product Line

Pipe Size (Range)
 Width (in)
 Length (in)
 Height (in)
 Pad Width (in)

Dimensional

1/2 in-1 in
 0.63
 2.25
 1.81
 0.63

General

Product Description

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1/2" - 1" Water Pipe

Conductor(s)

Copper Solid Size (Range)
 Copper Stranded (Range)
 Rebar Size (Range)

10 AWG-2 AWG
 10 AWG-2 AWG
 N/A

Physical

Type of Hardware
 Type of Plating
 Ground Strap
 Plated (Yes or No)
 For Armored Cable
 Product Material

Steel - Zinc Plated
 Unplated
 N
 N
 N
 Bronze Alloy

Recommended Installation Torque - Wire Clamp

50

Recommended Installation Torque - Pipe

50

Approvals / Certifications

UL Listed
 CSA Certified
 Rated for Direct Burial
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Y
 Y
 N
 Compliant
 N
 N
 UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Services

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM

Monday - Friday

Phone: 000-346-4175