



On Line Catalog



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

C22  
 781810142318  
 GRD CL BARE 1-1/4-2IN  
 Active

**Web Use**  
 BURNDY Product Line

Pipe Size (Range)  
 Width (in)  
 Length (in)  
 Height (in)  
 Pad Width (in)

**Dimensional**  
 1 1/4 in-2 in  
 0.75  
 3.63  
 2.38  
 1.00

Product Description

**General**  
 Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1-1/4" - 2" Water Pipe

Copper Solid Size (Range)  
 Copper Stranded (Range)  
 Rebar Size (Range)

**Conductor(s)**  
 10 AWG-2 AWG  
 10 AWG-2 AWG  
 N/A

Type of Hardware  
 Type of Plating  
 Ground Strap  
 Plated (Yes or No)  
 For Armored Cable  
 Product Material

**Physical**  
 DURIUM® Silicon Bronze  
 Unplated  
 N  
 N  
 N  
 Bronze Alloy

Recommended Installation Torque - Wire Clamp  
 Recommended Installation Torque - Pipe

50

50

**Approvals / Certifications**

UL Listed  
 CSA Certified  
 Rated for Direct Burial  
 ROHS Compatible  
 UL Recognized  
 CULUS  
 Industry Standards

Y  
 Y  
 N  
 Compliant  
 N  
 N  
 UL467

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47, industrial Park Drive  
 Manchester NH03109

**BURNDY Technical Services**

47, industrial Park Drive  
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
 Monday - Friday  
 Phone: 000-346-4175