



[On Line Catalog](#)



BURNDY Catalog Number
UPC Number
Description
Status

C22D
781810142356
GROUND CLAMP
Active

Web Use
BURNDY Product Line

Pipe Size (Range)
Width (in)
Length (in)
Height (in)
Pad Width (in)

Dimensional
1 1/4 in-2 in
0.75
3.63
2.38
1.00

Product Description

General
Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1-1/4" - 2" Water Pipe

Copper Solid Size (Range)
Copper Stranded (Range)
Rebar Size (Range)

Conductor(s)
10 AWG-2 AWG
10 AWG-2 AWG
N/A

Type of Hardware
Type of Plating
Ground Strap
Plated (Yes or No)
For Armored Cable
Product Material

Physical
DURIUM® Silicon Bronze
Unplated
N
N
N
Bronze Alloy

Recommended Installation Torque - Wire Clamp
Recommended Installation Torque - Pipe

50
50

Approvals / Certifications

UL Listed
CSA Certified
Rated for Direct Burial
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Y
Y
Y
Compliant
N
N
UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175