



[On Line Catalog](#)



BURNDY Catalog Number	C4
UPC Number	781810142325
Description	2-1/2 TO 4IN GRDCMP BARE
Status	Active

Web Use
BURNDY Product Line

Pipe Size (Range)	2 1/2 in-4 in
Width (in)	0.96
Length (in)	6.25
Height (in)	4.13
Pad Width (in)	1.88

Dimensional

General

Product Description
Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 2-1/2" - 4" Water Pipe

Conductor(s)

Copper Solid Size (Range)	10 AWG-2 AWG
Copper Stranded (Range)	10 AWG-2 AWG
Rebar Size (Range)	N/A

Physical

Type of Hardware	DURIUM® Silicon Bronze
Type of Plating	Unplated
Ground Strap	N
Plated (Yes or No)	N
For Armored Cable	N
Product Material	Bronze Alloy
Recommended Installation Torque - Wire Clamp	50
Recommended Installation Torque - Pipe	50

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
Rated for Direct Burial	N
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175