



On Line Catalog



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

GAR3902BU  
 781810001493  
 4-4/0, 1/2-1 IPS  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Width (in) 3.25  
 Length (in) 1.75  
 Height (in) 3.50  
 Size (Hex) or Size (Bolt) 3/8  
 Size (Hex) or Size (Bolt) - in 0.38  
 B Length (in) 1.75

**General**

Product Description Mechanical Grounding Connector,  
 Conductor to Water Pipe, 4-4/0  
 AWG, 1/2"-1" Pipe, 3/8" Stud

**Other**

Type of U Bolt 1031

**Approvals / Certifications**

UL Listed Y  
 CSA Certified Y  
 ROHS Compatible Compliant  
 UL Recognized N  
 CULUS N  
 Industry Standards UL467  
 Rated for Direct Burial Y

**Conductor(s)**

Copper Tube Size (SCH40) - Range 1/2-1  
 Rod Size (Range) N/A  
 Copper Solid Size (Range) N/A  
 Copper Stranded (Range) 4-4/0  
 Rebar Size (Range) N/A

**Physical**

Type of Hardware DURIUM® Silicon Bronze  
 Installation Torque 200  
 Type of Plating Unplated  
 Plated (Yes or No) N  
 Product Material Copper Alloy

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47, industrial Park Drive  
 Manchester NH03109

**BURNDY Technical Servcies**

47, industrial Park Drive  
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
 Monday - Friday  
 Phone: 000-346-4175