



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

HSB12T300PF
781810213735
25FTX 1/2IN BLK TW HTSHR
Active

Web Use
BURNDY Product Line

Dimensional
Dimension (Max Before Shrink) 0.50
Conductor Range #6-2
Wall Thickness 0.020

General
Heat Shrink Tubing, 0.50" ID Min.
(Exp.), 0.12" ID Max.(Rec.), 6-2
AWG, Cross Linked Polyolefin,
Thin Wall, Flame Retardant, Black,
600V

Conductor(s)
Nominal Diameter (Fraction) 1/2

Physical
Shrink Ratio 2:1
Color Black

Approvals / Certifications
UL Listed N
ROHS Compatible Compliant
UL Recognized Y
CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175