



[On Line Catalog](#)



BURNDY Catalog Number
UPC Number
Description
Status

HSB316T300PF
 781810213520
 25FTX 3/16INBLK TW HTSHR
 Active

Web Use
 BURNDY Product Line

	Dimensional
Dimension (Max Before Shrink)	0.19
Conductor Range	#18-12
Wall Thickness	0.020

	General
Product Description	Heat Shrink Tubing, 0.19" ID Min. (Exp.), 0.09" ID Max.(Rec.), 18-12 AWG, Cross Linked Polyolefin, Thin Wall, Flame Retardant, Black, 600V

	Conductor(s)
Nominal Diameter (Fraction)	3/16

	Physical
Shrink Ratio	2:1
Color	Black

	Approvals / Certifications
UL Listed	N
ROHS Compatible	Compliant
UL Recognized	Y
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175