


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YA26L2TC14E245
 781810019368
 CULUG-2/0STR-1/4X3/4-45D
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle 45 Degree
 Length (in) 2.65
 Tongue Type Standard
 Barrell Style Chamfered,Skived
 Bolt Hole Size (in) 0.27
 Barrel Type Standard
 Thickness 0.12
 B Length (in) 0.94
 Pad Width (in) 0.83
 E - in 0.75
 Strip Length 1

General

Number of Holes 2
 Product Description Cu compression tubular terminals-
 code conductor, 2 holes/W/ insp
 window, 2/0 AWG, 1/2" stud,Tin
 plated, Black, 13 index

Conductor(s)

Flex (Class G) Size - Range N/A
 Flex (Class H) Size - Range N/A
 Flex (Class I) Size - Range N/A
 Copper Solid Size (Range) N/A
 DLO Size (Range) N/A
 Copper Stranded (Range) 2/0 AWG

Physical

Type of Plating Tin - Electro Plated
 Bolt Hole Size 1/4
 Color Code Black
 Plated (Yes or No) Y
 Index Number 13
 Product Material Copper

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175