



On Line Catalog



**BURNDY Catalog Number**

YA26L90

**UPC Number**

781810018811

**Description**

2/0 CU 1-HOLE SHORT 90DE

**Status**

Active

**Web Use**

BURNDY Product Line

**Dimensional**

Tongue Angle 90 Degree  
 Length (in) 1.21  
 Tongue Type Standard  
 Barrell Style Chamfered  
 Bolt Hole Size (in) 0.39  
 Barrel Type Standard  
 Thickness 0.12  
 B Length (in) 0.94  
 Pad Width (in) 0.83  
 Strip Length 1

**General**

Number of Holes 1  
 Product Description Cu Tubing Cu Hylug; 1 Hole with Inspection Window; 2/0 AWG Code, 125 Navy; 600V-35kV; 3/8" stud; Standard; Compression; 0.40 in BCD; Black

**Conductor(s)**

Flex (Class G) Size - Range N/A  
 Flex (Class H) Size - Range N/A  
 Flex (Class I) Size - Range N/A  
 Copper Solid Size (Range) N/A  
 DLO Size (Range) N/A  
 Copper Stranded (Range) 2/0 AWG

**Physical**

Type of Plating Tin - Electro Plated  
 Color Code Black  
 Plated (Yes or No) Y  
 Index Number 13  
 Product Material Copper

**Approvals / Certifications**

UL Listed Y  
 CSA Certified Y  
 ROHS Compatible Compliant  
 UL Recognized N  
 CULUS N  
 Industry Standards UL467

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47, industrial Park Drive  
 Manchester NH03109

**BURNDY Technical Servcies**

47, industrial Park Drive  
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM

Monday - Friday  
 Phone: 000-346-4175