


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YA282LN
 781810503522
 4/0 CU 2-HOLE SHORT 1/2
 Active

Web Use
 BURNDY Product Line

Tongue Angle
 Length (in)
 Tongue Type
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 E - in
 Strip Length

Dimensional

Straight
 4.41
 Standard
 Chamfered, Skived
 0.52
 Standard
 0.14
 0.88
 1.02
 1.75
 1-1/8

Number of Holes

 Product Description

General

2
 Copper Compression Lug, 2 Hole
 w/ Inspection Window, 4/0 AWG,
 1/2" Stud, 1-3/4" Stud Hole
 Spacing, Short Barrel, Tin Plated

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

Conductor(s)

N/A
 N/A
 N/A
 N/A
 N/A
 4/0 AWG

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Physical

Tin - Electro Plated
 1/2
 Purple
 Y
 15
 Copper

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Approvals / Certifications

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175