



[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YA2CL2TC1445
 781810251287
 CULUG- 2STR-1/4X5/8-45DG
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle 45 Degree
 Length (in) 2.38
 Barrell Style Chamfered, Skived
 Bolt Hole Size (in) 0.27
 Barrel Type Standard
 Thickness 0.11
 B Length (in) 0.88
 Pad Width (in) 0.60
 E - in 0.63
 Strip Length 15/16

General

Number of Holes 2
 Product Description Cu code conductor std barrel, 2 Holes/W/insp W, #2AWG, 600V-35kV, 1/4" stud, Tin plated, Brown, 10 Index, UL Listed 90C

Conductor(s)

Flex (Class G) Size - Range N/A
 Flex (Class H) Size - Range N/A
 Flex (Class I) Size - Range N/A
 Copper Solid Size (Range) N/A
 DLO Size (Range) N/A
 Copper Stranded (Range) 2 AWG

Physical

Type of Plating Tin - Electro Plated
 Bolt Hole Size 1/4
 Color Code Brown
 Plated (Yes or No) Y
 Index Number 10
 Product Material Copper

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175