



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

YA34L2TC14E2
781810018286
CU HYLUG-500-1/4X3/4 C-C
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Dimensional

Straight
3.44
Standard
Chamfered,Skived
0.27
Standard
0.23
1.27
1.55
0.75
1-7/16

Number of Holes

Product Description

General

2
Cu Compression Terminal, 2 Holes
W/InspWindow, 500 kcmil Code,
1/4" Stud, 0.75" Spacing,
Standard Barrel

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

Conductor(s)

N/A
N/A
N/A
N/A
N/A
500 kcmil

Type of Plating
Color Code
Plated (Yes or No)
Index Number
Product Material

Physical

Tin
Brown
Y
20,299
Copper

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Approvals / Certifications

Y
Y
Compliant
N
N
UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175