


[On Line Catalog](#)
**BURNDY Catalog Number**

YA392LN

UPC Number

781810522073

Description

750 CU 2-HOLE SHORT NEMA

Status

Active

Web Use

BURNDY Product Line

Dimensional

Tongue Angle

Straight

Length (in)

5.36

Tongue Type

Standard

Barrell Style

Chamfered, Skived

Bolt Hole Size (in)

0.52

Barrel Type

Standard

Thickness

0.27

B Length (in)

1.42

Pad Width (in)

1.91

E - in

1.75

Strip Length

1-15/16

General

Number of Holes

2

Product Description

Cu Comp Terminal Code Cond, Bvl
Entry, 2 Hole/W/InspWindow, 750
kcmil Str Code, 600 V-35 kV, 1/2"
Stud, 1.75" Spacing, Std bbl, Tin
Plated, Black, 24 Index

Conductor(s)

Flex (Class G) Size - Range

N/A

Flex (Class H) Size - Range

N/A

Flex (Class I) Size - Range

N/A

Copper Solid Size (Range)

N/A

DLO Size (Range)

N/A

Copper Stranded (Range)

750 kcmil

Physical

Type of Plating

Tin - Electro Plated

Bolt Hole Size

1/2

Color Code

Black

Plated (Yes or No)

Y

Index Number

24

Product Material

Copper

Approvals / Certifications

UL Listed

Y

CSA Certified

Y

ROHS Compatible

Compliant

UL Recognized

N

CULUS

N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM

Monday - Friday

Phone: 000-346-4175