




On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

YA40L2NTCFX
781810056745
CUHYLUG 650FLX NEMA TNG
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Dimensional
Straight
5.38
Standard
Chamfered
0.52
Standard
0.30
1.42
1.98
1.75
1-5/16

Number of Holes

General
2
Cu Comp Terminal Flex Cond, Bvl
Entry, 2 Hole/W/InspWindow, 646
kcmil(1600/#24)DLO, 650 kcmil
Flex, 600 V-35 kV, 1/2" Stud,
1.75" Spacing, Std bbl

Product Description

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

Conductor(s)
650
650
650
N/A
646 (1600/#24)
650

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Physical
Tin
1/2
Black
Y
24
Copper

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Approvals / Certifications
Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175