



[On Line Catalog](#)



BURNDY Catalog Number
UPC Number
Description
Status

YA442NFXB
781810053584
750, LONG, BELLED, NEMA
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Number of Holes

Product Description

Flex (Class M) Size - Range
Aircraft Cable Size (Range)
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)
Flex (Class G) Size - Range

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Documentation

Dimensional

Straight
7.44
Standard
Belled
0.52
Long
0.33
3.33
2.19
1.75
3-7/16

General

2
Copper Compression Lug, 2 Hole
w/o Inspection Window, 777.7
Flex, 1/2" Stud, 1-3/4" Stud Hole
Spacing, Long Barrel, Belled End,
Tin Plated

Conductor(s)

N/A
N/A
N/A
N/A
N/A
777.7 (1925/#24) DLO
N/A
N/A
N/A

Physical

Tin - Electro Plated
1/2
Yellow
Y
L115
Copper

Approvals / Certifications

Y
Y
Compliant
N
N

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175

