



[On Line Catalog](#)



BURNDY Catalog Number
UPC Number
Description
Status

YA462NFXB
781810038949
BELLED CU LUG-1000 FLEX-
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Dimensional
Straight
7.91
Standard
Belled
0.52
Long
0.39
3.58
2.69
1.75
3-11/16

Number of Holes

Product Description

General
2
Copper Compression Lug, 2 Hole
w/o Inspection Window, 1111
Flex, 1/2" Stud, 1-3/4" Stud Hole
Spacing, Long Barrel, Belled End,
Tin Plated

Aircraft Cable Size (Range)
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)
Flex (Class G) Size - Range
Flex (Class M) Size - Range

Conductor(s)
N/A
1111
1111
N/A
1111 (2750/#24)
N/A
1000 kcmil
1111
1111

Type of Plating
Bolt Hole Size
Plated (Yes or No)
Index Number
Product Material

Physical
Tin - Electro Plated
1/2
Y
29
Copper

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Approvals / Certifications
Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

BURNDY Technical Servcies

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175

47, industrial Park Drive
Manchester NH03109

47, industrial Park Drive
Manchester NH03109

