



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

YA4C2LN
781810501474
4 STR CU 2-HOLE SHORT NE
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Dimensional

Straight
4.14
Standard
Chamfered,Skived
0.52
Standard
0.12
0.81
0.83
1.75
7/8

Number of Holes

General

2
Copper Compression Lug, 2 Hole
w/ Inspection Window, 4 AWG,
1/2" Stud, 1-3/4" Stud Hole
Spacing, Short Barrel, Tin Plated

Product Description

Conductor(s)

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

N/A
N/A
N/A
N/A
N/A
4 AWG

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin - Electro Plated
1/2
Gray
Y
8,346
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175