


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YA6C2LN
 781810501863
 CULUG- 6 STR-SHORT-NEMA
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle Straight
 Length (in) 4.10
 Tongue Type Standard
 Barrell Style Chamfered, Skived
 Bolt Hole Size (in) 0.52
 Barrel Type Standard
 Thickness 0.12
 B Length (in) 0.54
 Pad Width (in) 0.83
 E - in 1.75
 Strip Length 5/8

General

Number of Holes 2
 Product Description Copper Compression Lug, 2 Hole
 w/ Inspection Window, 6 AWG,
 1/2" Stud, 1-3/4" Stud Hole
 Spacing, Short Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range N/A
 Flex (Class H) Size - Range N/A
 Flex (Class I) Size - Range N/A
 Copper Solid Size (Range) N/A
 DLO Size (Range) N/A
 Copper Stranded (Range) 6 AWG

Physical

Type of Plating Tin - Electro Plated
 Bolt Hole Size 1/2
 Color Code Blue
 Plated (Yes or No) Y
 Index Number 7,374
 Product Material Copper

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM

Monday - Friday
 Phone: 000-346-4175