


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YA6CL2TC1490
 781810019023
 CULUG-6STR-1/4X5/8-90DEG
 Active

Web Use
 BURNDY Product Line

Tongue Angle
 Length (in)
 Tongue Type
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 E - in
 Strip Length

Dimensional

90 Degree
 1.51
 Standard
 Chamfered,Skived
 0.27
 Standard
 0.08
 0.54
 0.45
 0.63
 5/8

Number of Holes

 Product Description

General

2
 Cu code conductor std barrel, 2
 Holes/W/insp W, #6AWG, 600V-
 35kV, 1/4" stud, Tin plated, Blue,
 7 or 374 Index , UL Listed 90C

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

Conductor(s)

N/A
 N/A
 N/A
 N/A
 N/A
 N/A
 6 AWG

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Physical

Tin - Electro Plated
 1/4
 Blue
 Y
 7,374
 Copper

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Approvals / Certifications

Y
 Y
 Compliant
 N
 N
 UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175