


[On Line Catalog](#)

Photo Not Available



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YA6CL2TC14E245  
 781810273081  
 CULUG-6STR-1/4X3/4-45DEG  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Tongue Angle 45 Degree  
 Length (in) 1.91  
 Barrell Style Chamfered  
 Bolt Hole Size (in) 0.25  
 Barrel Type Standard  
 Thickness 0.08  
 B Length (in) 0.54  
 Pad Width (in) 0.45  
 E - in 0.50  
 Strip Length 5/8

**General**

Number of Holes 2  
 Product Description Cu compression tubular terminals-  
 code conductor, 2 holes/W/ insp  
 window, #6 AWG, 1/2" stud, Tin  
 plated, Blue, 7 Index

**Conductor(s)**

Flex (Class G) Size - Range N/A  
 Flex (Class H) Size - Range N/A  
 Flex (Class I) Size - Range N/A  
 Copper Solid Size (Range) N/A  
 DLO Size (Range) N/A  
 Copper Stranded (Range) 6 AWG

**Physical**

Type of Plating Tin  
 Color Code Blue  
 Plated (Yes or No) Y  
 Index Number 7,374  
 Product Material Copper

**Approvals / Certifications**

UL Listed Y  
 CSA Certified Y  
 ROHS Compatible Compliant  
 UL Recognized N  
 CULUS N  
 Industry Standards UL468A-468B

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47, industrial Park Drive  
 Manchester NH03109

**BURNDY Technical Servcies**

47, industrial Park Drive  
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
 Monday - Friday  
 Phone: 000-346-4175