



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

YA6CL345
781810018736
6 STR CU 1-H SHORT 45DEG
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
Strip Length

Dimensional
45 Degree
1.33
Standard
Chamfered,Skived
0.33
Standard
0.07
0.54
0.52
9/16
General
1
Cu code conductor standard
barrel, Single hole/W/ insp
window, #8 AWG, #6 Sol, 3/8"
stud, Red, 49 index, 5/16" stud,
Tin plated, Blue, 7 or 374 index

Number of Holes

Product Description

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

Conductor(s)
N/A
N/A
N/A
N/A
N/A
6 AWG

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Physical
Tin - Electro Plated
5/16
Blue
Y
7,374
Copper

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Approvals / Certifications
Y
Y
Compliant
N
N
UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175