


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YA6CL4BOX
 781810553107
 6 STR CU 1-HOLE SHORT 3/
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle
 Length (in)
 Tongue Type
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 Strip Length

Straight
 1.62
 Standard
 Chamfered,Skived
 0.39
 Standard
 0.06
 0.54
 0.63
 9/16
General
 1
 Copper Compression Lug, 1 Hole
 w/ Inspection Window, 6 AWG,
 3/8" Stud, Short Barrel, Tin Plated

Number of Holes
 Product Description

Conductor(s)

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

N/A
 N/A
 N/A
 N/A
 N/A
 6 AWG

Physical

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Tin - Electro Plated
 3/8
 Blue
 Y
 7,374
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175