



[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YA8CL2TC1445
 781810044278
 CULUG-8STR-(2)1/4 STUDS-
 Active

Web Use
 BURNDY Product Line

Tongue Angle
 Length (in)
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 E - in
 Strip Length

Dimensional

45 Degree
 1.94
 Chamfered,Skived
 0.27
 Standard
 0.08
 0.44
 0.44
 0.63
 1/2

Number of Holes

General

2
 Cu compression tubular terminals-
 code conductor, 2 holes/W/ insp
 window, #8 AWG;#8
 Weld;37/24;#6 Sol, 1/2" stud, Tin
 plated, Red, 49 index

Product Description

Conductor(s)

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

8 AWG
 8 AWG
 8 AWG
 N/A
 8 (37/#24) DLO
 8 AWG

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Physical

Tin
 1/4
 Red
 Y
 49
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Y
 Y
 Compliant
 N
 N
 UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175