



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

YA8CL2TC14E190
 781810019252
 CULUG- 8 STR-1/4X1-90DEG
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle 90 Degree
 Length (in) 1.87
 Tongue Type Standard
 Barrell Style Chamfered,Skived
 Bolt Hole Size (in) 0.27
 Barrel Type Standard
 Thickness 0.08
 B Length (in) 0.44
 Pad Width (in) 0.44
 E - in 1.00
 Strip Length 1/2

General

Number of Holes 2
 Product Description Cu compr™ code std bbrl, 2 hole, #8 AWG, 600 V to 35kV, Chamfered, 1/4" stud

Conductor(s)

Flex (Class G) Size - Range 8 AWG
 Flex (Class H) Size - Range 8 AWG
 Flex (Class I) Size - Range 8 AWG
 Copper Solid Size (Range) N/A
 DLO Size (Range) 8 (37/#24) DLO
 Copper Stranded (Range) 8 AWG

Physical

Type of Plating Tin
 Bolt Hole Size 1/4
 Color Code Red
 Plated (Yes or No) Y
 Index Number 49
 Product Material Copper

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175