




On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

YA8CLBOX
781810525661
8 STR CU 1-HOLE SHORT 8-
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
Strip Length

Dimensional
Straight
1.16
Standard
Chamfered
0.20
Standard
0.08
0.44
0.41
7/16

Number of Holes

General
1
Copper Compression Lug, 1 Hole
w/ Inspection Window, 8-6 AWG,
#8-#10 Stud, Short Barrel, Tin
Plated

Product Description

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

Conductor(s)
N/A
N/A
N/A
6 AWG
N/A
8 AWG

Type of Plating
Color Code
Plated (Yes or No)
Index Number
Product Material

Physical
Tin - Electro Plated
Red
Y
49
Copper

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Approvals / Certifications
Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175