





On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

YAEV10T3
781810564271
12-10 NYL. HVY DTY RING
Active

Web Use
BURNDY Product Line

Length (in)
Tongue Type
Stud Size (in)
Pad Width (in)

Dimensional
1.30
Ring
1/4
0.47

Max Voltage Rating

Electrical
600

Product Description

General
Copper Terminal; Ring Tongue w/
Inspection Hole; Wire Range 12-
10 AWG; 1/4" Stud; Nylon
Insulated; Short Barrel; Tin Plated;
600 Volts Max.

Aircraft Cable Size (Range)
Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

Conductor(s)
AN 12-AN 10
N/A
N/A
12-10

Type of Plating
Connector Type
Color Code
Insulation Type
Plated (Yes or No)

Physical
Tin
Terminal
Yellow
Nylon
Y

Industry Standards
UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Approvals / Certifications
Military Specified (Mil-
Spec),UL486
Y
N
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175