


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YAL1CT14
 781810416884
 CDN 1STR 1/4STUD SHORT
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	1.58
Barrell Style	Chamfered
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.10
B Length (in)	0.73
Pad Width (in)	0.68

General

Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, 1 AWG, 1/4" Stud, Short Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	1 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Green
Plated (Yes or No)	Y
Index Number	11
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175