



On Line Catalog



BURNDY Catalog Number	YAL1CT516
UPC Number	78181041690
Description	CANLUG-#1 STR-SHORT-5/16
Status	null

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)

Dimensional
Straight
1.73
Standard
Chamfered
0.33
Standard
0.1
0.73
0.68

Number of Holes

Copper Stranded (Range)
Copper Solid Size (Range)

General
1
Conductor(s)
1
N/A

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Physical
Tin - Electro Plated
5/16
Green
Y
11
Copper

Industry Standards
UL Listed
CSA Certified
ROHS Compatible
UL Recognized

Approvals / Certifications
UL468A-468B
Yes,Y
Yes,Y
Compliant
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175