



[On Line Catalog](#)



BURNDY Catalog Number
UPC Number
Description
Status

YAV10R
 781810025208
 12-10 HVYDTY RING 8-10 S
 Active

Web Use
 BURNDY Product Line

Strip Length
 Length (in)
 Tongue Type
 Stud Size (in)
 Pad Width (in)

Dimensional

5/16
 0.53
 Ring
 #10,#8,#9
 0.38

General

Copper Right Angle Compression
 Lug, 12-10 AWG w/ Inspection
 Hole, #8-#10 Stud, Electro-Tin
 Plated

Product Description

Conductor(s)

Aircraft Cable Size (Range)
 Copper Solid Size (Range)
 Navy Cable Size (Range)
 Copper Stranded (Range)

AN 12-AN 10
 N/A
 N/A
 12-10

Physical

Type of Plating
 Connector Type
 Plated (Yes or No)

Tin - Electro Plated
 Terminal - Ring
 Y

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Services

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175