



[On Line Catalog](#)

	BURNDY Catalog Number	YAV10RBOX
	UPC Number	781810021743
	Description	RING- 12- 10 AWG-UNIN
	Status	Active
	Web Use	
	BURNDY Product Line	
		Dimensional
	Tongue Angle	Straight
	Length (in)	0.53
	Tongue Type	Ring
	Barrell Style	Chamfered
	Barrel Type	Standard
	Thickness	0.06
	B Length (in)	0.38
	Pad Width (in)	0.38
	Strip Length	3/8"
		General
	Number of Holes	1
	Product Description	Copper Ring Terminal, 12 - 10 AWG, #8 - #10 Stud, Electro-Tin Plated
		Conductor(s)
	Flex (Class G) Size - Range	N/A
	Flex (Class H) Size - Range	N/A
	Flex (Class I) Size - Range	N/A
	Copper Solid Size (Range)	13-10
	DLO Size (Range)	N/A
	Copper Stranded (Range)	14-10
		Physical
	Type of Plating	Tin
	Plated (Yes or No)	Y
	Product Material	Copper
		Approvals / Certifications
	UL Listed	Y
	CSA Certified	Y
	ROHS Compatible	Compliant
	UL Recognized	N
	CULUS	N
		Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175