



On Line Catalog



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YAV14T1BOX  
 781810533505  
 RING- 20- 14 AWG-UNIN  
 Active

**Web Use**  
 BURNDY Product Line

Length (in)  
 Tongue Type  
 Stud Size (in)  
 Pad Width (in)  
 Strip Length

**Dimensional**

0.79  
 Ring  
 #6,#8  
 0.31  
 9/32"

**General**

Seamless uninsulated  
 Compression Heavy Duty Ring  
 Tongue Terminal, 20-14 Str.20-12  
 Sol., 6-8, .31 in L, .79 in W, Tin  
 Electro plated

Product Description

**Other**

Non-Ratchet:Y10D, Y10-  
 22Ratchet:MR8G98, MR8-  
 9Q,Y8MRB-1, MR20  
 YAV14T1

Installation Tooling

Bulk Package

**Approvals / Certifications**

UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS  
 Industry Standards

Y  
 Y  
 Compliant  
 N  
 N  
 UL467

**Conductor(s)**

Aircraft Cable Size (Range)  
 Copper Solid Size (Range)  
 Navy Cable Size (Range)  
 Copper Stranded (Range)

AN 20-AN 14  
 20-12  
 2 1/2 (1)-4 (41)  
 20-14

**Physical**

Type of Plating  
 Connector Type  
 Plated (Yes or No)

Tin - Electro Plated  
 Terminal - Ring  
 Y

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47, industrial Park Drive  
 Manchester NH03109

**BURNDY Technical Servcies**

47, industrial Park Drive  
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
 Monday - Friday  
 Phone: 000-346-4175