



On Line Catalog



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YAV1CL2NTCFX  
781810249949  
CULUG (225/24)-2 NEMA  
Active

**Web Use**  
BURNDY Product Line

Tongue Angle  
Length (in)  
Barrell Style  
Bolt Hole Size (in)  
Barrel Type  
Thickness  
B Length (in)  
Pad Width (in)  
E - in  
Strip Length

**Dimensional**

Straight  
4.04  
Chamfered,Skived  
0.52  
Standard  
0.11  
0.62  
0.83  
1.75  
11/16

Number of Holes

**General**

2  
Cu Comp Terminal, 2- Nema Holes  
W/InspWindow, #1 Weld, #1 AWG  
Code, 75 Navy, 1/2" Stud,  
Standard Barrel

Product Description

**Conductor(s)**

Flex (Class G) Size - Range  
Flex (Class H) Size - Range  
Flex (Class I) Size - Range  
Copper Solid Size (Range)  
DLO Size (Range)  
Copper Stranded (Range)

1 AWG  
1 AWG  
1 AWG  
N/A  
1 (225/#24) DLO  
1 AWG

Type of Plating  
Bolt Hole Size  
Color Code  
Plated (Yes or No)  
Index Number  
Product Material

**Physical**

Tin - Electro Plated  
1/2  
Green  
Y  
11  
Copper

**Approvals / Certifications**

UL Listed  
CSA Certified  
ROHS Compatible  
UL Recognized  
CULUS

Y  
Y  
Compliant  
N  
N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47, industrial Park Drive  
Manchester NH03109

**BURNDY Technical Servcies**

47, industrial Park Drive  
Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
Monday - Friday  
Phone: 000-346-4175