



[On Line Catalog](#)

Photo Not Available



BURNDY Catalog Number
UPC Number
Description
Status

YAV25L2TC14E1FX
 781810276105
 1/0FLEX 1/4STUD E=1IN
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	2.76
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.12
B Length (in)	0.69
Pad Width (in)	0.83
E - in	1.00
Strip Length	11/16

General

Number of Holes	2
Product Description	Cu Tubing Hylug; 2 Holes with Inspection Window; 1/0 AWG Flex,100 Navy; 600V-35kV; 1/4" stud; Standard; Compression; 0.27 in BCD; Pink

Conductor(s)

Flex (Class G) Size - Range	1/0 AWG
Flex (Class H) Size - Range	1/0 AWG
Flex (Class I) Size - Range	1/0 AWG
Copper Solid Size (Range)	N/A
DLO Size (Range)	1/0 (275/#24) DLO
Copper Stranded (Range)	1/0

Physical

Type of Plating	Tin
Bolt Hole Size	1/4
Color Code	Pink
Plated (Yes or No)	Y
Index Number	12
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM

Monday - Friday

Phone: 000-346-4175