




On Line Catalog

 	BURNDY Catalog Number	YAV26L2NTCFX
	UPC Number	781810021781
	Description	HYLUG - 2/0 FLEX - NEMA
	Status	Active
	Web Use	
	BURNDY Product Line	
	Dimensional	
	Tongue Angle	Straight
	Length (in)	4.31
	Tongue Type	Standard
	Barrell Style	Chamfered,Skived
	Bolt Hole Size (in)	0.52
	Barrel Type	Standard
	Thickness	0.13
	B Length (in)	0.81
	Pad Width (in)	0.93
	E - in	1.75
	Strip Length	13/16
	General	
	Number of Holes	2
	Product Description	Copper Compression Lug, 2 Hole w/ Inspection window, 2/0 Flex, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel, Tin Plated
	Conductor(s)	
	Flex (Class G) Size - Range	2/0 AWG
	Flex (Class H) Size - Range	2/0 AWG
	Flex (Class I) Size - Range	2/0 AWG
	Copper Solid Size (Range)	N/A
	DLO Size (Range)	2/0 (375/#24) DLO
	Copper Stranded (Range)	2/0 AWG
	Physical	
	Type of Plating	Tin
	Bolt Hole Size	1/2
	Color Code	Black
	Plated (Yes or No)	Y
	Index Number	13
	Product Material	Copper
	Approvals / Certifications	
	UL Listed	Y
	CSA Certified	Y
	ROHS Compatible	Compliant
	UL Recognized	N
	CULUS	N
	Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175