



[On Line Catalog](#)



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YAV27L20  
 781810129845  
 3/0 HVYDTY RING-5/16STUD  
 Active

**Web Use**  
 BURNDY Product Line

Tongue Angle  
 Length (in)  
 Tongue Type  
 Pad Width (in)

**Dimensional**

Straight  
 2.45  
 Ring  
 1.03

**General**

Copper Compression Lug, Ring  
 Tongue, 1 Hole w/ Inspection  
 Hole, AN-3/0, 5/16" Stud, Short  
 Barrel, Tin Plated

**Conductor(s)**

Product Description

AN 000  
 N/A  
 N/A  
 N/A

Aircraft Cable Size (Range)  
 Copper Solid Size (Range)  
 Navy Cable Size (Range)  
 Copper Stranded (Range)

**Physical**

Type of Plating  
 Connector Type  
 Plated (Yes or No)

Tin  
 Terminal  
 Y

**Approvals / Certifications**

Industry Standards

UL467, Military Specified (Mil-  
 Spec)

UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 Mil-Spec Class Code  
 CULUS

Y  
 Y  
 Compliant  
 N  
 Class 1  
 N

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47, industrial Park Drive  
 Manchester NH03109

**BURNDY Technical Servcies**

47, industrial Park Drive  
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
 Monday - Friday  
 Phone: 000-346-4175