


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YAV27LTC14FX
 781810022481
 CU-HYDENT 3/0 FLEX 1/4 S
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle
 Length (in)
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 Strip Length

Straight
 2.15
 Chamfered
 0.27
 Standard
 0.14
 1.00
 1.03
 1

General

Number of Holes

 Product Description

1
 Cu Tubing Compression Terminal,
 1 Hole W/InspWindow, 3/0 AWG
 Class G-M, 3/0 (450/#24)DLO, 3/0
 AWG Class B, C Code, 150 Navy,
 1/4" Stud, Standard Brll

Conductor(s)

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

3/0 AWG
 3/0 AWG
 3/0 AWG
 N/A
 3/0 (450/#24) DLO
 3/0 AWG

Physical

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Tin - Electro Plated
 1/4
 Orange
 Y
 14
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175