


[On Line Catalog](#)
**BURNDY Catalog Number**

YAV28L2TC38FX90

UPC Number

781810021880

Description

CU HYDENT-4/0 FLEX-90DEG

Status

Active

Web Use

BURNDY Product Line

Dimensional

Tongue Angle	90 Degree
Length (in)	2.34
Tongue Type	Standard
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.15
B Length (in)	1.03
Pad Width (in)	1.14
E - in	1.00
Strip Length	1-1/16

General

Number of Holes	2
Product Description	Cu Tubing Hylug; 2 Holes with Inspection window; 4/0 AWG Flex,200 Navy; 600V-35kV; 3/8" stud; Standard; Compression;Purple

Conductor(s)

Flex (Class G) Size - Range	4/0 AWG
Flex (Class H) Size - Range	4/0 AWG
Flex (Class I) Size - Range	4/0 AWG
Copper Solid Size (Range)	N/A
DLO Size (Range)	4/0 (550/#24) DLO
Copper Stranded (Range)	4/0 AWG

Physical

Type of Plating	Tin
Bolt Hole Size	3/8
Color Code	Purple
Plated (Yes or No)	Y
Index Number	15
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175