


[On Line Catalog](#)
**BURNDY Catalog Number****UPC Number****Description****Status**

YAV28TC38FXB

781810080832

BELLED HYLUG-4/0 FLEX-3/

Active

Web Use

BURNDY Product Line

Dimensional

Tongue Angle

Straight

Length (in)

3.19

Tongue Type

Standard

Barrell Style

Belled

Bolt Hole Size (in)

0.39

Barrel Type

Long

Thickness

0.14

B Length (in)

1.77

Pad Width (in)

1.14

Strip Length

1-7/8

General

Number of Holes

1

Product Description

Copper Compression Lug, 1 Hole
w/o Inspection Window, 4/0 AWG
/ 250 FLEX, 3/8" Stud, Long
Barrel, Belled End, Tin Plated**Conductor(s)**

Aircraft Cable Size (Range)

N/A

Flex (Class H) Size - Range

4/0 AWG

Flex (Class I) Size - Range

4/0 AWG

Copper Solid Size (Range)

N/A

DLO Size (Range)

4/0 (550/#24) DLO

Navy Cable Size (Range)

200 (61) Navy

Copper Stranded (Range)

4/0 AWG

Flex (Class G) Size - Range

1/0 AWG

Flex (Class M) Size - Range

4/0 AWG

Physical

Type of Plating

Tin - Electro Plated

Bolt Hole Size

3/8

Color Code

Yellow

Plated (Yes or No)

Y

Index Number

16

Product Material

Copper

Approvals / Certifications

UL Listed

Y

CSA Certified

Y

ROHS Compatible

Compliant

UL Recognized

N

CULUS

N

Industry Standards

UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA47, industrial Park Drive
Manchester NH03109**BURNDY Technical Servcies**47, industrial Park Drive
Manchester NH03109Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175

