


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YAV2CL2TC14FX45
 781810022214
 CULUG-2FLEX-1/4X5/8-45DG
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle 45 Degree
 Length (in) 2.22
 Tongue Type Standard
 Barrell Style Chamfered
 Bolt Hole Size (in) 0.27
 Barrel Type Standard
 Thickness 0.10
 B Length (in) 0.63
 Pad Width (in) 0.68
 E - in 0.63
 Strip Length 11/16

General

Number of Holes 2
 Cu Tubing Hylug; 2 Holes with Inspection Window; #2 AWG Flex, 60 Navy; 600V-35kV; 1/4" stud; Standard; Compression; 0.27 in BCD; Brown

Conductor(s)

Flex (Class G) Size - Range 2 AWG
 Flex (Class H) Size - Range 2 AWG
 Flex (Class I) Size - Range 2 AWG
 Copper Solid Size (Range) 2 AWG
 DLO Size (Range) 3 (125/#24) DLO-2 (150/#24) DLO
 Copper Stranded (Range) 2 AWG

Physical

Type of Plating Tin - Electro Plated
 Bolt Hole Size 1/4
 Color Code Brown
 Plated (Yes or No) Y
 Index Number 10
 Product Material Copper

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Services

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175