


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YAV2CLTC12FX90
 781810275535
 2FLEX 1/2STUD 90DG
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle 90 Degree
 Length (in) 1.40
 Barrell Style Chamfered
 Bolt Hole Size (in) 0.52
 Barrel Type Standard
 Thickness 0.09
 B Length (in) 0.63
 Pad Width (in) 0.73
 Strip Length 11/16

General

Number of Holes 1
 Product Description Cu Tubing Hylug; 1 Hole with Inspection Window; #2 WELD, 3(125/#24)-2(150/#24) DLO, #2 AWG Code, 60 Navy; 600V-35kV; 1/2" stud; Compression; 0.53 in BCD

Conductor(s)

Flex (Class G) Size - Range 2 AWG
 Flex (Class H) Size - Range 2 AWG
 Flex (Class I) Size - Range 2 AWG
 Copper Solid Size (Range) 2 AWG
 DLO Size (Range) 3 (125/#24) DLO-2 (150/#24) DLO
 Copper Stranded (Range) 2 AWG

Physical

Type of Plating Tin - Electro Plated
 Bolt Hole Size 1/2
 Color Code Brown
 Plated (Yes or No) Y
 Index Number 10
 Product Material Copper

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175