




[On Line Catalog](#)

 	BURNDY Catalog Number	YAV4CL2TC14E1FX
	UPC Number	781810044537
	Description	4FLEX 1/4STUD E=1IN
	Status	Active
	Web Use	
	BURNDY Product Line	
	Dimensional	
	Tongue Angle	Straight
	Length (in)	2.45
	Barrell Style	Chamfered
	Bolt Hole Size (in)	0.27
	Barrel Type	Standard
	Thickness	0.09
	B Length (in)	0.50
	Pad Width (in)	0.55
	E - in	1.00
	Strip Length	9/16
	Number of Holes	2
	Product Description	Copper Compression Lug, 2 Hole w/ Inspection Window, 4 Flex, 1/4" Stud, 1" Stud Hole Spacing, Short Barrel, Tin Plated
	Conductor(s)	
	Flex (Class G) Size - Range	4 AWG
	Flex (Class H) Size - Range	4 AWG
	Flex (Class I) Size - Range	4 AWG
	Copper Solid Size (Range)	4 AWG
	DLO Size (Range)	5 (91/#24) DLO-4 (105/#24) DLO
	Copper Stranded (Range)	4 AWG
	Physical	
	Type of Plating	Tin - Electro Plated
	Bolt Hole Size	1/4
	Color Code	Gray
	Plated (Yes or No)	Y
	Index Number	8
	Product Material	Copper
	Approvals / Certifications	
	UL Listed	Y
	CSA Certified	Y
	ROHS Compatible	Compliant
	UL Recognized	N
	CULUS	N
	Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175