


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YAV4CL2TC38FX90
 781810054161
 CUHYLUG 4STR FLEX 2)3/8
 Active

Web Use
 BURNDY Product Line

Tongue Angle
 Length (in)
 Tongue Type
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 E - in
 Strip Length

Dimensional

90 Degree
 2.11
 Standard
 Chamfered
 0.39
 Standard
 0.08
 0.50
 0.58
 1.00
 9/16

Number of Holes

General

2
 Cu Tubing Hylug; 2 Holes with
 Inspection window; #4 AWG
 Flex, 40 & 50 Navy; 600V-35kV;
 3/8" stud; Standard; Compression;
 0.40 in BCD; Gray

Product Description

Conductor(s)

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

4 AWG
 4 AWG
 4 AWG
 4 AWG
 5 (91/#24) DLO-4 (105/#24) DLO
 4 AWG

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Physical

Tin - Electro Plated
 3/8
 Gray
 Y
 8
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Services

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175