




On Line Catalog



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YAZ272TC14E2  
 781810227855  
 CULUG-3/0STR-LONG W/PORT  
 Active

**Web Use**  
 BURNDY Product Line

Tongue Angle  
 Length (in)  
 Tongue Type  
 Barrell Style  
 Bolt Hole Size (in)  
 Barrel Type  
 Thickness  
 B Length (in)  
 Pad Width (in)  
 E - in  
 Strip Length

**Dimensional**

Straight  
 3.36  
 Standard  
 Skived  
 0.27  
 Long  
 0.12  
 1.50  
 0.90  
 0.75  
 1-9/16

Number of Holes  
 Product Description

**General**

2  
 Copper Compression Lug, 2 Hole  
 w/ Inspection Window, 3/0 AWG,  
 1/4" Stud, 3/4" Stud Hole  
 Spacing, Long Barrel, Tin Plated

Copper Solid Size (Range)  
 Navy Cable Size (Range)  
 Copper Stranded (Range)

**Conductor(s)**

3/0 AWG  
 150 (61) Navy  
 3/0 AWG

Type of Plating  
 Bolt Hole Size  
 Color Code  
 Plated (Yes or No)  
 Index Number  
 Product Material

**Physical**

Tin - Electro Plated  
 1/4  
 Orange  
 Y  
 14  
 Copper

UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS

**Approvals / Certifications**

Y  
 Y  
 Compliant  
 N  
 N

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47, industrial Park Drive  
 Manchester NH03109

**BURNDY Technical Servcies**

47, industrial Park Drive  
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
 Monday - Friday  
 Phone: 000-346-4175