



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

YAZ2CTC516
 781810243435
 CULUG- 2 STR-LONG W/PORT
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle
 Length (in)
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 Strip Length

Straight
 2.27
 Skived
 0.33
 Long
 0.11
 1.25
 0.60
 1-5/16

General

Number of Holes
 Product Description

1
 Cu Tubing Hylug (One Hole Code);
 1 Hole with Inspection Window;
 #2 AWG Code,60 Navy; 600V-
 35kV; 5/16" stud; Long;
 Compression; 0.33 in BCD; Brown

Conductor(s)

Copper Solid Size (Range)
 Navy Cable Size (Range)
 Copper Stranded (Range)

N/A
 60 (37) Navy
 2 AWG

Physical

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Tin - Electro Plated
 5/16
 Brown
 Y
 10
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175