



On Line Catalog



BURNDY Catalog Number	YAZ6C2TC14E190
UPC Number	781810228890
Description	CULUG- 6AWG-LONG W/PORT
Status	Active
Web Use	
BURNDY Product Line	
	Dimensional
Tongue Angle	90 Degree
Length (in)	1.88
Tongue Type	Standard
Barrell Style	Skived
Bolt Hole Size (in)	0.27
Barrel Type	Long
Thickness	0.08
B Length (in)	1.12
Pad Width (in)	0.45
E - in	1.00
Strip Length	1-3/16
	General
Number of Holes	2
	2 Hole HYLUG Cu Compr
Product Description	Terminal, Long Brll, W/ Insp
	Window, #6 AWG, 30 NAVY, 1/4"
	stud, 1" spacing, Blue, 7 or 374
	Index
	Conductor(s)
Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	30 (19) Navy
Copper Stranded (Range)	6 AWG
	Physical
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7,374
Product Material	Copper
	Approvals / Certifications
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175