


[On Line Catalog](#)

Photo Not Available



BURNDY Catalog Number
UPC Number
Description
Status

YAZV2C2TC38FX90
 781810176450
 CULUG-2FLX-LNG W/SKV-90D
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle 90 Degree
 Strip Length 1-7/16
 Length (in) 2.17
 Barrell Style Skived
 Bolt Hole Size (in) 0.39
 Barrel Type Long
 Thickness 0.10
 B Length (in) 1.38
 Pad Width (in) 0.68
 E - in 1.00

General

Number of Holes 2
 Cu compression long barrel flex
 conductor, 2 holes/W/ insp
 window, #2 weld(125/24-150/24),
 #2AWG,3/8" stud, Tin
 plated,Brown, 10 index

Conductor(s)

Copper Solid Size (Range) N/A
 Navy Cable Size (Range) N/A
 Copper Stranded (Range) 2 AWG

Physical

Type of Plating Tin
 Bolt Hole Size 3/8
 Color Code Brown
 Plated (Yes or No) Y
 Index Number 10
 Product Material Copper

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM

Monday - Friday
 Phone: 000-346-4175