


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YGHA252N
 781810220610
 CU 1/0 HVY DUTY GRD TERM
 Active

Web Use
 BURNDY Product Line

Thickness
 B Length (in)
 D - in
 Pad Width (in)
 Stud Size (Fraction)
 E - in

Dimensional

0.19
 0.83
 3.00
 0.91
 1/2
 1.75

General

Product Description

Copper Compression Lug, Heavy
 Duty, 2 Hole w/ Inspection Probe
 Hole, 1/0 AWG, 1/2" Stud, 1.75"
 Stud Hole Spacing, Short Barrel

Conductor(s)

Copper Solid Size (Range)
 Copper Stranded (Range)

N/A
 1/0

Physical

Type of Plating
 Connector Type
 Plated (Yes or No)
 Index Number

Unplated
 Terminal
 N
 14

Approvals / Certifications

Rated for Direct Burial
 UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Y
 Y
 Y
 Compliant
 N
 N
 UL468A-468B,UL467,IEEE 837

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175