



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

YS28LBOX
781810556757
4/0 STR. HYLINK-SPLICE
Active

Web Use
BURNDY Product Line

Strip Length
Barrell Style
Barrel Type

Dimensional

1-1/16
Chamfered
Standard

General

Copper Compression Splice, 4/0
AWG, 2.32" Splice Length, Short
Barrel, Tin Plated

Physical

Tin - Electro Plated
Y
15
Copper

Product Description

Type of Plating
Plated (Yes or No)
Index Number
Product Material

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards
Documentation

Y
Y
Compliant
N
N
UL468A-468B

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175