



On Line Catalog

Photo Not Available



BURNDY Catalog Number
UPC Number
Description
Status

YSL27
 781810418833
 CANADA YSL SPLICE 3/0STR
 Active

Web Use
 BURNDY Product Line

Strip Length
 Barrell Style
 Barrel Type

Dimensional

1-1/16
 Chamfered
 Standard

General

Copper Compression Splice, 3/0
 AWG (Str), 2.30" Splice Length,
 Short Barrel, Tin Plated

Product Description

Physical

Type of Plating
 Plated (Yes or No)
 Index Number
 Product Material

Tin - Electro Plated
 Y
 14,101
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175